

EasyReach™ Cleaning Tool

Contec's lightweight stainless steel EasyReach™ Cleaning Tool is designed for cleaning isolators, LAF hoods, glove boxes and other mini environments. Its rectangular shape makes overlapping straight-line action easy to achieve. Hinged joint along with the ability to lay flat makes this lightweight tool comfortable and easy to use for accessing hard-to-reach areas.




The single-use, multilayer cleaning pads are very absorbent, ensuring good even coverage of disinfectant or IPA. The easy grab edge on the cleaning pad ensures the pad fits tightly on the mop frame but is easy to replace with gloved hands. Sterile knitted pads presaturated with 70% IPA are also available.



Features	Benefits
Versatile and easy to use	<ul style="list-style-type: none"> • Specially designed cleaning pad tab/grip enables quick and easy fitting to the frame with gloved hands • All tool options are designed to be easily passed through transfer hatches • Versatile low profile, lay flat pivoting head ensures even the most awkward areas can be quickly reached with ease • Presaturated cleaning pad option removes the need for 70% IPA spray, minimizing transfer of materials and simplifying the cleaning procedure
Safe for users and equipment	<ul style="list-style-type: none"> • Reduces the risk of operators leaning into LAF hoods, opening isolators, intervening into RABS, and introducing contamination while attempting to ensure effective cleaning • Knitted presaturated pad option reduces operator exposure to high levels of VOCs typically experienced when using IPA spray bottles and reduces the volume of hazardous chemical storage • Rounded tool edges and strong, durable, double layer pads ensure equipment is not damaged during use • All components are designed to be chemical resistant, minimizing the risk of contamination from degradation
Sewn edges	<ul style="list-style-type: none"> • Pads are sewn to generate less particles and fibers while remaining strong, durable, and compatible with common cleanroom solutions • The polyester cleaning pads leave no unwanted surface residues • Well-fitted quilted pad ensures effective, even surface coverage reducing the number of viable and nonviable contaminants and ensuring maximum residue removal

Part No.	Description	Packaging
MEQT0001	EasyReach™ Cleaning Pads, quilted polyester, 7.5" x 2.8" (19x7cm)	4/bag; 15 bags/case
MEQT0002SZ	EasyReach™ Cleaning Pads, quilted polyester, 7.5" x 2.8" (19x7cm), sterile	4/bag; 15 bags/case
PSME0001	EasyReach™ 100% Knitted Polyester Cleaning Pads, 7.5" x 2.8" (19x7cm), presaturated with 70% IPA, sterile	8/bag; 8 bags/case
2665LF	EasyReach™ Lay Flat Cleaning Tool, 16.5" (42cm), stainless steel, lightweight, 1 piece	1/case
2685LF	QuickConnect™ EasyReach™ lay flat mop head frame, 7.5" (19cm), stainless steel	1/case
2685P	QuickConnect™ EasyReach™ lay flat mop frame, 7.5" (19cm), polypropylene	1/case
2642	QuickConnect™ Anodized Aluminum Telescopic Handle, 16" - 30" (41-76cm)	1/case
2644	QuickConnect™ Stainless Steel Telescopic Handle, 16" - 30" (41-76cm)	1/case
2686	QuickConnect™ Stainless Steel Handle with Hanging Loop, 16" (41cm)	1/case

Product Information

Cover material MEQT0001, MEQT0002SZ 2685LF, 2665LF 2685P	100% knitted polyester Type 304 stainless steel Polypropylene (PP) 
Cover construction	Multilayer quilted; sewn
Packaging Materials	Outer bags (OB1, OB2), low density polyethylene (LDPE)  Case (CS), corrugated fiberboard (PAP) 
Environment	ISO 4-8 Grade A/B for sterile, C/D for nonsterile
Shelf life	Sterile: 2 years from manufacturing date



Technical Data






Attribute (units)	Typical Value	Test Method
Mop weight, dry; (g)	20.4	Contec Method
Sorbent capacity; (mL/mop)	63	CTM004-03
Particles, P ≥0.5µm; (x10 ⁶ /m ²)	5.4	IEST-RP-CC004.2, Sec. 5.1
Fibers > 100µm; (x10 ³ /m ²)	0.10	IEST-RP-CC004.2, Sec. 5.2
Compatible Mop Frames	2685LF, 2665LF, 2665SF, 2685P	

Packaging

	EA/OB1	OB1/OB2	OB2/CS	EA/CS
MEQT0001	4	1	15	60
MEQT0002SZ	4	1	15	60

EA = Each, OB1 = Outer Bag 1, OB2 = Outer Bag 2, CS = Case

Recycle Symbol Key

PET	
HDPE	
LDPE	
PP	
PAP	

Notes

- The data shown are typical values and should not be used as product specifications.
- Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
- Current and/or comparison data may be available. Please contact a Contec sales representative for details.
- CTM – Refers to Contec Test Method
- Mop Coverage data is based on mop head applying solution such that the mopped surface is visibly wetted across the full mop path with no dry streaking observed, under controlled conditions. It is the responsibility of the user to determine appropriate coverage to ensure surfaces are visibly wet for the contact time required for their specific solution.